

Manual

Actuator **ID10**



Revision 2023.08_V2.1


Technical changes may be made to improve the product without notice!



CAUTION



• Be sure that the load acts on the actuator in the axial direction and it isn't recommended to have side load acts on the actuator.



- If the actuator is jammed by an obstruction or the load is severely overweight, the actuator's clutch
 protection device will trip and run idly to protect the actuator or the customer's mechanical
 equipment from damage. Please be careful to avoid obstructions and do not exceed the rated load
 of the actuator.
- Users are forbidden to open the outer cover of the limit switch so as not to affect the original protection level of the actuator, resulting in the immediate failure of the original factory protection commitment.



MANUAL DRIVE (MD) CONNECTOR


The MD (manual drive) is an alternative way to drive the motor directly, if the power is not available.

Step 1. Remove the plug on the gearbox cover.

Step 2. Use a 8.0mm hex bit or electric screwdriver (recommended) to drive the gear directly.

Step 3. Insert the plug into the hole, and confirm the plug is installed properly.

• The Max. drive torque is 6kg-cm with 4500N load.(Ball Screw)





WIRE CONNECTION

For ID10 actuator, connection rule of power wires varies according to different types and gear ratio(s). Please follow the instructions below.

(1) Basic (Without limit switch nor positioning feedback)

• Gear ratio: 5:1, 10:1, 20:1

	Wire color	Definition	Descriptions
Power	Red		Connect red wire to "Vdc +" & black wire to "Vdc -" of DC power to extend the actuator. Switch the polarity of DC input to retract it.
wires	Black		

• Gear ratio: 30:1, 40:1

	Wire color	Definition	Descriptions
Power wires	Red	DC power	Connect red wire to "Vdc -" & black wire to "Vdc +" of DC power to extend the actuator. Switch the polarity of DC input to retract it.
	Black		

(2) With limit switches

	Wire color	Definition	Descriptions
Power	Red		Connect red wire to "Vdc +" & black wire to "Vdc -" of DC power to extend the actuator. Switch the polarity of DC input to retract it.
wires	Black		

(3) With single Hall effect sensor positioning feedback

	Wire color	Definition	Descriptions
Power wires	Red	DC power	Connect red wire to "Vdc +" & black wire to "Vdc -" of DC power to extend the actuator. Switch the polarity of DC input to retract it.
	Black		
Signal wires	White	Vin	Voltage input range: 5 ~ 20V
	Yellow	Hall output	High= Input - 1.2V (±0.6V) Low= GND Hall signal data: High Low Hall Hall Hall Hall effect sensor resolution: 20ppi, 1.27mm/pulse (0.787pulses/mm)
	Blue	GND	



(4) With Potentiometer (POT) absolute positioning feedback

	Wire color	Definition	Descriptions
Power wires	Red Black	DC power	Connect red wire to "Vdc +" & black wire to "Vdc -" of DC power to extend the actuator. Switch the polarity of DC input to retract it.
	Yellow	Vin	Input voltage 70V max.
Signal wires	Blue	POT output	1. Potentiometer specification: - 10K ohm, 10 turns Tolerance ±5% 2. Output voltage: The voltage (resistance) between blue and white increases linearly from about 0 when the actuator extends, and decreases when it retracts. B W Actuator extends 3. There are different resolutions according to the stroke length (as table below) Stroke (mm) Resistance (Tolerance: ±0.3KΩ) 102 (4") 0.3 ~ 8.1K 153 (6") 0.3 ~ 9.2K 203 (8") 0.3 ~ 9.2K 254 (10") 0.3 ~ 8.8K 457 (18") 0.3 ~ 9.4K 610 (24") 0.1 ~ 9.9K
	White	GND	

SAFETY DECLARATION

This appliance cannot be used by children or persons with reduced physical, sensory or mental capabilities, or lack of experience and knowledge, unless they have been given supervision or instruction.